

Trimmer Mower

Commercial
Power Tools

Model: TR45080GMNG
UPC: 843530005806

GENERAC PRO TRIMMER MOWER

- Powerful walk-behind trimmer capable of tackling the heaviest mowing demands.
- Reliable OHV engine.
- Oversize wheels for easy maneuverability.
- Ample 22 in (56 cm) cutting width.
- Three adjustable mowing heights between 2.0–3.25 in (5.1–8.3 cm).
- Offset frame design makes easy work of trimming along foundations, fence lines, and other obstacles with precise control.
- Cast aluminum front nose plate to guard against damage.



FEATURES






- **Generac G-Force Engine:** Powerful, easy starting engines make our trimmer mowers the natural choice for any task, and are designed for long life.
- **Heavy-Duty Cutting Cords:** Sized up to 225 mil (5.72 mm), for reliability you can count on. 175 mil (4.4 mm) cord is included.
- **Engineered to Perform:** A rock solid performer, backed by over 25 years of innovation, and tested for thousands of hours. Every detail is designed to deliver great reliability and performance.
- **Anti-Wrap Trimmer Head:** prevents tangled vegetation and provides less down time.
- **QUICK-LOCK™ Trimmer Head:** Trimmer cord changes take just seconds. Simply insert the cord into the unique gripping mechanism to anchor it in place.

Specifications

General	
Type	Push
Cutting	
Cutting Height	2.0–3.25 in (adjustable) (5.1–8.3 cm)
Cutting Width	22 in (56 cm)
Cord Thickness	225 mil (5.72 mm) maximum 175 mil (4.4 mm) included
Engine	
Make	Generac G-Force
Air Filter Element	Paper
Cooling Method	Air cooled
Displacement	10.6 in ³ (174cc)
Engine Type	OHV
Torque	8.0 ft-lbs (10.8 Nm) (Gross torque per SAE J1940)
Lubrication	Splash
Number of Cylinders	1
Oil Capacity	10–17 oz (0.3–0.5 L)
Oil Type	SAE 30W HD
Starting Type	Manual

Dimensions	
Shipping Dimensions	35 in x 22.25 in x 24 in (88.9 cm x 56.5 cm x 60.9 cm)
Shipping Weight	81 lbs (36.7 kg)
Weight	71 lbs (32.2 kg)
Width	21.5 in (54.6 cm)
Handlebar height	31–49 in (78.7–124.5 cm)
Fuel System	
Fuel Capacity	1.6 qt (1.5 L)
Material	
Frame	14 gauge steel
Wheels/Tires	
Dimensions	16 in (30.5 cm), resin
Number of Tires	2
Warranty	
Machine / Engine	1 year

Available Accessories

	Model #	Product	Description
	416941	Premium Generac Pro Trimmer Cord (225-mil [5.72 mm] Sawtooth Cord, 82 ft [25 m] Roll)	Extreme trimming power. The 225-mil (5.72 mm) Sawtooth Trimmer Cord is thicker, tougher, and longer-lasting than any other cord available – anywhere. The durable material and serrated design allows you to cut through the toughest weeds and brambles. Exclusively designed for the Quick-Lock Trimmer Head.
	356331	Quick-Lock™ Pre-Cut Cord (155-mil [3.9 mm] green, 13 in [33 cm], 48 Pk)	Pre-cut cords cut to the perfect length for the Quick-Lock Trimmer Head. Be ready in a flash when you need a new cord in the field with pre-cut lengths of specially-formulated 155-mil (3.9 mm) green cutting cord.
	356321	Quick-Lock™ Pre-Cut Cord (175-mil [4.4 mm] blue, 13 in [33 cm], 48 Pk)	Pre-cut cords cut to the perfect length for the Quick-Lock Trimmer Head. Be ready in a flash when you need a new cord in the field with pre-cut lengths of specially-formulated 175-mil (4.4 mm) blue spiral cutting cord. Includes 48 pre-cut cords.
	416971	DuraBlade® Kit for Trimmer Mower	Increase your Trimmer Mower's versatility, by turning into a light brush and bramble cutter. Generac Pro DuraBlades slice through 3/8 in (9.5 mm) thick woody material and tough weeds with ease.
	416981	TrimSafe Guard Kit, TR4	Trim without the worries of damaging plants, trees, and fences. Our TrimSafe guard mounts quickly and easily.